

CC-304B

Heating Circulator Bath with housing, bath and all moistened parts are made of stainless steel. With cooling coil for watercooling (3/8"), pressure- and suction pump made of high-resistant plastic. With adjustable overtemperature protection according to DIN 12876.

Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-2 warranty - registration required.

Technical data according to DIN 12876

from Serial-No.:	279431	1.2/17
max. ambient temperature	40 °C	
min. ambient temperature	5 °C	
Degree of Protection	IP20	
Fuse (1 phase)	16 A	
max. current	14 A	
Power supply requirement	230V 1~ 50/60Hz	
Net weight	14 kg	
Overall dimensions WxDxH **	210x335x392 mm	
Height of bath opening	194 mm	
Bath depth	155 mm	
Width bath opening WxD	130x100 mm	Order-No.: 2005.0001.01
Bath volume	5	
min. filling capacity	3,2	
max. permissible kin. viscosity	50 mm²/s	
Pump connection	M16x1 male	Industr ©
Delivery suction pressure (head)	0,4 bar	
max. delivery (suction)	18,5 l/min	
Suction pump	yes	
Delivery pressure (head)	0,7 bar	-
max. delivery	25 l/min	Party and a second seco
Pressure pump		
Heating power	3 kW	
Safety classification	Class III / FL	
	Device), RS232	CC 304
Interface digital	Ethernet, USB (Host u.	
External sensor	Pt100	
Temperature control internal	Pt100	
Absolute accuracy	setup for calibration	
temperature set point / display	5,7" colour Touchscreen	Statement and a statement of the
Temperature stability at 70°C	0,02 K	
with refrigerator	-20 °C	
Operating temperature range	28300 °C	

1.2/17

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Technical data according to DIN 12876

Accessories and periphery: mini-USB cable #54949*, Adapter nom. dia 12 mm*, bath cover*, dummy plugs*, sleeve nuts thread M16x1 *, connection tube silicon*, power supply cable*, connection tubes, drain valve

* standard equipment

Output data valid for: Room temperature 20°C In accordance with EN60034-1 the following voltage and frequency tolerances are valid: Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction. Example: -10% voltage and + 3% frequency -> not allowed ! -10% voltage and -3% frequency -> allowed.

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single-phase devices (230V/115V) -> with cable and plug

2. Three-phase devices with current consumption less than 63A -> with cable, without plug

3. Three-phase devices with current consumption greater than 63A -> without cable, without plug

** Please respect space requirements. See operating conditions at www.huber-online.com