huber

Unichiller 080T

Chiller with air-cooled refrigerating unit and circulation pump (stainless steel). Housing, atmospheric open expansion tank and copper soldered evaporator made of stainless steel. With digital level indicator. For externally closed applications.

Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-2 warranty - registration required.

Technical data according to DIN 12876

Operating temperature range temperature set point / display Internal temperature sensor Sensor external connection Interface digital

Temperature stability at -10°C Safety classification Cooling power

at 15°C at 0°C at -10°C

Refrigeration machine

Refrigerant

Refrigerant quantity Circulation pump: max. delivery

max. delivery pressure Delivery at 0,33 bar Delivery at 0,5 bar Delivery at 1,0 bar Delivery at 1,5 bar Delivery at 2,0 bar

Delivery at 2,5 bar Delivery at 3,0 bar Delivery at 3,5 bar

Delivery at 4,0 bar Delivery at 4,5 bar Delivery at 5,0 bar

Delivery at 5,5 bar Pump connection min. filling capacity

Volume of expansion
Overall dimensions WxDxH **

Net weight

sound pressure level +/- 4 dB(A)

-10...40 °C

5,7" colour Touchscreen

Pt100 Pt100

Ethernet, USB (Host u. Device), RS232

0,5 K Class I / NFL

8 kW 4,8 kW 2,5 kW

air-cooled, CFC- and

HCFC-free R507 3,7 kg C3

84 l/min 5,6 bar 81 l/min

79 l/min 74 l/min 69 l/min 64 l/min

58 l/min 52 l/min

46 I/min 39 I/min 30 I/min

21 l/min 7 l/min G1 1/4 male

5 I 7,5 I

600x790x1614 mm

254 kg 66 dB(A)



Order-No.: 3016.0001.01

Technical data according to DIN 12876

from Serial-No.:	190948	1.0/13
max. ambient temperature	40 °C	
min. ambient temperature	5 °C	
Degree of Protection	IP20	
Fuse (3 phase)	3x10 A	
max. current (3 Phase)	8 A	
Power supply (3 Phase)	400V 3~ 50Hz *	

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original. Accessories and periphery: mini-USB cable #54949*, Hose coupling for G1 1/4 male*, cover expansion tank*, connection tubes, Com.G@te.

Output data valid for: Room temperature 20°C

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and +2% frequency -> not allowed! -5% voltage and -2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

- 1. Single-phase devices (230V/115V) -> with cable and plug
- 2. Three-phase devices with current consumption less than 63A -> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A -> without cable, without plug
- ** Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau AG Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com

^{*} standard equipment