Unichiller 045T

Chiller with air-cooled refrigerating unit and circulation pump (industrial plastic material). Housing, atmospheric open expansion tank and copper soldered evaporator made of stainless steel. With digital level indicator. For externally closed applications.

Pilot ONF:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-2 warranty - registration required.

Technical data according to DIN 12876

-20...40 °C Operating temperature range temperature set point / display 5,7" colour Touchscreen Internal temperature sensor Pt100 Sensor external connection Pt100 Interface digital Ethernet, USB (Host u. Device), RS232 Temperature stability at -10°C 0.5 K Safety classification Class I / NFL Cooling power at 15°C 4,5 kW at 0°C

4,5 kW at -10°C 2,9 kW at -20°C 1,5 kW air-cooled, CFC- and Refrigeration machine **HCFC-free**

Refrigerant R507 Refrigerant quantity 1,8 kg Circulation pump: В max. delivery 26 I/min max. delivery pressure 3.0 bar Delivery at 0.5 bar 20 I/min 16 l/min Delivery at 1,0 bar 12 l/min Delivery at 1,5 bar Delivery at 2,0 bar 8 I/min G3/4 male Pump connection min. filling capacity 3,5 I Volume of expansion 3.51

Overall dimensions WxDxH ** 500x552x1451 mm

Net weight 164 kg Power supply (3 Phase) 400V 3~ 50Hz * max. current (3 Phase) 5,5 A Fuse (3 phase) 3x10 A Degree of Protection IP20 min. ambient temperature 5°C max. ambient temperature 40 °C



Order-No.: 3014.0002.01

from Serial-No.: 305396 1.1/18

Technical data according to DIN 12876

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original. Accessories and periphery: mini-USB cable #54949*, Hose coupling for G3/4 male*, cover expansion tank*, connection tubes, Com.G@te.

* standard equipment

Output data valid for: Room temperature 20°C

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Special Case: Acetone and Polyglycol: The plastic pump is not resistant against acetone and polyglycols (depending on the manufacturer). It is recommended that water is mixed with either glysantine or ethylene glycol for freeze protection. A more resistant plastic is available on request at an additional cost.

Standard delivery conditions - Power cable configuration:

- 1. Single-phase devices (230V/115V) -> with cable and plug
- 2. Three-phase devices with current consumption less than 63A -> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A -> without cable, without plug
- ** Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau AG Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com