

## PUREÕÜŴ HPLC






- Űæc^} c^åÁversaÔæ}iÁc^&@;[∥[\*^Á ]¦[çãa^•Ás@Á¦^¢ãa∥ãcÁ;Ás;c^¦&@æ}\*^Ë æà|^Ás[}}^&c[!•
- ″Ú|`\*•Á\$,&|`å^åÁ{¦Áæ|Á}}`•^åÁ;[¦œ
- Ő^]^}åāj\*Áj}Ásej]|ä&æsāj}ÁÒZØ|[¸íÁş^}c -ālc'¦Ájã^Ás²&|^Ájæáspâ^

## Made in the USA



Á∰PUREÕÜÓJ°ÁPÚŠÔÁ[|ç^}σÁ^•^¦ç[ãÁ&æ]Áæ)åÁæ]cd^Áæ••^{ à|ā⟩•Á
[~~\Áω@Áæ••^6α)åÁ;[•σÁ\\*[}[{ æÁæàÁæ¢∂Áē]cd^Áæ••^{ à|ā⟩•Á
ð,å\*•d^ÈÁ/@•^Áæ••^{ à|ā⟩•Á8[{ ^Á, ãc@ÁæàÁæ¢∂Á[|\* α¾}Áæ,Aæ}é
ð,å\*•d^ÈÁ/@•^Áæ••^{ à|ā⟩•Á8[{ ^Á, ãc@ÁæàÁæ¢∂æ³}¢³ÁVersaÔæ]°Á¢\&@Ë
}[|[\*^ÊÆÁÔ|æ•ÁXŒÁUVØÒÁTæ)ã[|åÁæ)åÁæ)ÅŒÃÁQ|^σÁXæ¢,Áæ[{ ྠ^åÁ
åc@ÁæÁZ[¢¢ÁGÍ{ ÊÆÈÈQ↓{ ÁÚVØÒÁZâ\Á[¦ÁæAÁæ}[¦ÁÃdæã]}¦ÁÃdææã]}È

ÁÁÁÁV @ Á ^ æ ^ å ÁVersa Ôæ ª ª å ^ • ã } Á | ã ā æ ~ • Áš à ^ Áç ã æ ª · Áæ å Á ^ | ã ā æ ~ • Áš à ^ • Á | [ { Á | ãã ā \* Áā Áæ å Á \* ó Áæ ÁS[ } ææ } ^ \ ÉÉ \* ã @ Á PÚŠÔÁÜ ^ • ^ | ç [ ā ÁOĒ • ^ { à | ã \* Áā Áæ Á\* æ æ ¢ ^ å Ág Á\* ^ ó æ & ¿ | æ \* Áā ææ Á ~ | [ { Á [ ` | Áæ æ å • ã Á ã @ Áæ Áæ á æ æ ó Aæ Á • ā \* Áæ Á ) | æ • Á K QÁÚ V Ø Ó Á Tæ à ã | å Áæ å å Á Ô @ { ã & æ | ^ ÁÜ ^ • ã æ æ ó Aæ ã } Å Ú ÉÜ ā \* ÈÁ



- The air inlet valve blocks vapors of the solution in the container by utilizing an internal check valve. When the pressure reaches a specific psi, the valve will open allowing for the container to have adequate flow rate. It will keep the lab space safe from the solution.
- 3A Flangeless nuts, in combination
- with an inverted PTFE ferrule, create a leak-free seal around
- the tubing. Sizes are compatible with all 1/4"-28 flat-bottom ports.
- 4 Class VI PTFE EZwaste® puck
- 5 Class VI VersaCap® 45mm, Open Top For Use With Machined Manifolds, Natural PP
- 6 Class VI PTFE Manifold and Chemically Resistant Viton O-Ring











# Foxx Life Sciences 45X SKU's

450-XXXX-FLS - HPLC Upstream Cap Assembly SKU's Each SKU Comes With:

	1	Foxx Life Sciences VersaCap* GL45	4	Foxx Life Sciences Corresponding Fitting Pack
2	2	Foxx Life Sciences Class VI PTFE Reservoir Adapter	5	Foxx Life Sciences Safety Air Inlet Valve
(	3	Foxx Life Sciences, O-Ring, VersaCap* GL45, Black, Viton	6	Foxx Life Sciences EZFlow* Hydrophobic PTFE Vent Filter

#### 45R-XXXX-FLS / 45V-XXX-FLS - HPLC Upstream Clear & Amber Bottle Assembly SKU's Each SKU Comes With:

	1	Foxx Life Sciences VersaCap* GL45	4	Foxx Life Sciences Corresponding Fitting Pack
	2	Foxx Life Sciences Class VI PTFE Reservoir Adapter	5	Foxx Life Sciences Safety Air Inlet Valve
	3	Foxx Life Sciences, O-Ring, VersaCap* GL45, Black, Viton	6	Foxx Life Sciences EZFlow* Hydrophobic PTFE Vent Filter
7	7A	Foxx Life Sciences Clear Glass Bottle with GL45 VersaCap*, USP Type 1 Borosilicate 3.3 Bottle	7B	Foxx Life Sciences Amber Glass Bottle with GL45 VersaCap*, USP Type 1 Borosilicate 3.3 Bottle

## 38-430 Cap Assemblies

450-0300-FLS	HPLC Reservoir Cap Assembly, 38-430, Glass Bottle Adapter, x3 3.2mm (1/8") and 1.6mm (1/16") Ports	
450-0301-FLS	HPLC Reservoir Cap Assembly, 38-430, Glass Bottle Adapter, x2 3.2mm (1/8") and 1.6mm (1/16") Ports	
450-0302-FLS	HPLC Reservoir Cap Assembly, 38-430, Glass Bottle Adapter, x1 3.2mm (1/8") and 1.6mm (1/16") Ports	

## **GL45 Cap Assemblies**

**Foxx** 

450-0600-FLS	HPLC Reservoir Cap Assembly, VersaCap* GL45, O-Ring Adapter, x6 3.2mm (1/8*) and 1.6mm (1/16*) Ports
450-0601-FLS	HPLC Reservoir Cap Assembly, VersaCap* GL45, O-Ring Adapter, x4 3.2mm (1/8") and 1.6mm (1/16") Ports
450-0602-FLS	HPLC Reservoir Cap Assembly, VersaCap* GL45, O-Ring Adapter, x3 3.2mm (1/8") and 1.6mm (1/16") Ports
450-0603-FLS	HPLC Reservoir Cap Assembly, VersaCap* GL45, O-Ring Adapter, x2 3.2mm (1/8") and 1.6mm (1/16") Ports
450-0604-FLS	HPLC Reservoir Cap Assembly, VersaCap* GL45, O-Ring Adapter, x1 3.2mm (1/8*) and 1.6mm (1/16*) Ports

#### GL45 Bottle Assemblies, 500mL, Clear PUREGRIP® Bottle

45R-4600-FLS	HPLC Reservoir Assembly, 500mL PUREGRIP" Bottle, Reagent, Clear, VersaCap" GL45, Class VI PTFE Adapter, x6 3.2mm (1/8") and 1.6mm (1/16") Ports
45R-4601-FLS	HPLC Reservoir Assembly, 500mL PUREGRIP" Bottle, Reagent, Clear, VersaCap" GL45, Class VI PTFE Adapter, x4 3.2mm (1/8") and 1.6mm (1/16") Ports
45R-4602-FLS	HPLC Reservoir Assembly, 500mL PUREGRIP" Bottle, Reagent, Clear, VersaCap" GL45, Class VI PTFE Adapter, x3 3.2mm (1/8") and 1.6mm (1/16") Ports
45R-4603-FLS	HPLC Reservoir Assembly, 500mL PUREGRIP" Bottle, Reagent, Clear, VersaCap" GL45, Class VI PTFE Adapter, x2 3.2mm (1/8") and 1.6mm (1/16") Ports
45R-4604-FLS	HPLC Reservoir Assembly, 500mL PUREGRIP* Bottle, Reagent, Clear, VersaCap* GL45, Class VI PTFE Adapter, x1 3.2mm (1/8") and 1.6mm (1/16") Ports

### GL45 Bottle Assemblies, 1000mL, Clear PUREGRIP® Bottle

HPLC Reservoir Assembly, 1000mL PUREGRIP" Bottle, Reagent, Clear, VersaCap" GL45, Class VI PTFE Adapter, x6 3.2mm (1/8") and 1.6mm (1/16") Ports
HPLC Reservoir Assembly, 1000mL PUREGRIP" Bottle, Reagent, Clear, VersaCap" GL45, Class VI PTFE Adapter, x4 3.2mm (1/8") and 1.6mm (1/16") Ports
HPLC Reservoir Assembly, 1000mL PUREGRIP" Bottle, Reagent, Clear, VersaCap" GL45, Class VI PTFE Adapter, x3 3.2mm (1/8") and 1.6mm (1/16") Ports
HPLC Reservoir Assembly, 1000mL PUREGRIP" Bottle, Reagent, Clear, VersaCap" GL45, Class VI PTFE Adapter, x2 3.2mm (1/8") and 1.6mm (1/16") Ports
HPLC Reservoir Assembly, 1000mL PUREGRIP" Bottle, Reagent, Clear, VersaCap" GL45, Class VI PTFE Adapter, x1 3.2mm (1/8") and 1.6mm (1/16") Ports

#### GL45 Bottle Assemblies, 2000mL, Clear PUREGRIP® Bottle

45R-6600-FLS	HPLC Reservoir Assembly, 2000mL PUREGRIP" Bottle, Reagent, Clear, VersaCap* GL45, Class VI PTFE Adapter, x6 3.2mm (1/8") and 1.6mm (1/16") Ports
45R-6601-FLS	HPLC Reservoir Assembly, 2000mL PUREGRIP" Bottle, Reagent, Clear, VersaCap* GL45, Class VI PTFE Adapter, x4 3.2mm (1/8") and 1.6mm (1/16") Ports
45R-6602-FLS	HPLC Reservoir Assembly, 2000mL PUREGRIP" Bottle, Reagent, Clear, VersaCap* GL45, Class VI PTFE Adapter, x3 3.2mm (1/8") and 1.6mm (1/16") Ports
45R-6603-FLS	HPLC Reservoir Assembly, 2000mL PUREGRIP" Bottle, Reagent, Clear, VersaCap* GL45, Class VI PTFE Adapter, x2 3.2mm (1/8") and 1.6mm (1/16") Ports
45R-6604-FLS	HPLC Reservoir Assembly, 2000mL PUREGRIP" Bottle, Reagent, Clear, VersaCap" GL45, Class VI PTFE Adapter, x1 3.2mm (1/8") and 1.6mm (1/16") Ports

#### GL45 Bottle Assemblies, 500mL, Amber PUREGRIP® Bottle

45V-4600-FLS	HPLC Reservoir Assembly, 500mL PUREGRIP* Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x6 3.2mm (1/8") and 1.6mm (1/16") Ports
45V-4601-FLS	HPLC Reservoir Assembly, 500mL PUREGRIP* Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x4 3.2mm (1/8") and 1.6mm (1/16") Ports
45V-4602-FLS	HPLC Reservoir Assembly, 500mL PUREGRIP* Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x3 3.2mm (1/8") and 1.6mm (1/16") Ports
45V-4603-FLS	HPLC Reservoir Assembly, 500mL PUREGRIP" Bottle, Reagent, Amber, VersaCap" GL45, Class VI PTFE Adapter, x2 3.2mm (1/8") and 1.6mm (1/16") Ports
45V-4604-FLS	HPLC Reservoir Assembly, 500mL PUREGRIP* Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x1 3.2mm (1/8") and 1.6mm (1/16") Ports

#### GL45 Bottle Assemblies, 1000mL, Amber PUREGRIP® Bottle

45V-5600-FL	HPLC Reservoir Assembly, 1000mL PUREGRIP" Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x6 3.2mm (1/8") and 1.6mm (1/16") Ports
45V-5601-FL	HPLC Reservoir Assembly, 1000mL PUREGRIP* Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x4 3.2mm (1/8*) and 1.6mm (1/16*) Ports
45V-5602-FL	HPLC Reservoir Assembly, 1000mL PUREGRIP* Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x3 3.2mm (1/8*) and 1.6mm (1/16*) Ports
45V-5603-FL	HPLC Reservoir Assembly, 1000mL PUREGRIP* Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x2 3.2mm (1/8*) and 1.6mm (1/16*) Ports
45V-5604-FL	HPLC Reservoir Assembly, 1000mL PUREGRIP" Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x1 3.2mm (1/8") and 1.6mm (1/16") Ports

### GL45 Bottle Assemblies, 2000mL, Amber PUREGRIP® Bottle

	45V-6600-FLS	HPLC Reservoir Assembly, 2000mL PUREGRIP" Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x6 3.2mm (1/8") and 1.6mm (1/16") Ports
	45V-6601-FLS	HPLC Reservoir Assembly, 2000mL PUREGRIP" Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x4 3.2mm (1/8") and 1.6mm (1/16") Ports
	45V-6602-FLS	HPLC Reservoir Assembly, 2000mL PUREGRIP" Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x3 3.2mm (1/8") and 1.6mm (1/16") Ports
	45V-6603-FLS	HPLC Reservoir Assembly, 2000mL PUREGRIP" Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x2 3.2mm (1/8") and 1.6mm (1/16") Ports
	45V-6604-FLS	HPLC Reservoir Assembly, 2000mL PUREGRIP" Bottle, Reagent, Amber, VersaCap* GL45, Class VI PTFE Adapter, x1 3.2mm (1/8") and 1.6mm (1/16") Ports













