## LS Class Reciprocating Pump



CE

### High Performance Isocratic Pumps

The reliable **LS Class** consists of single-headed, positive displacement piston pumps incorporating advanced cam designs for very low pulsation. With micro-stepping motor technology and a proven single-piston pump mechanism, the LS Class exceeds the performance of more expensive units at a fraction of the cost.

The pumps are ideal for a wide variety of HPLC applications (including Bio-compatible separations), Semi-Prep LC, metering & dispensing, and general laboratory use. Standard fluid path materials are Stainless Steel and PEEK. With 5 mL/min, 10 mL/min and 40 mL/min versions available, and pressure capability up to 6,000 psi, these versatile pumps will meet the most demanding applications.

Features include automatic pressure compensation, Pulse Dampener, integrated Prime-Purge Valve, interactive keypad control, and complete PC control and status through RS-232C, micro-USB, and Ethernet serial communications. The unique LS Class provides the highest performance/cost ratio in a compact package.



SP-

Stainless Steel & PEEK Fluid Path Material Available



Drip Tray & Leak Sensor

# FLOW RATE PRESSURE FLUID PATH CONTROL

5 mL/min 10 mL/min 40 mL/min Up to 6,000 psi (5 mL/min or 10 mL/min) Stainless Steel, or PEEK

RS-232, Micro USB, Ethernet, Run/Stop, Analog (0-10 V, 4-20 mA)



Components are also available in Kit Form for OEM Applications.

#### **LS Class Specifications**

	5 mL/min	10 mL/min	40 mL/min
Flow Rate Range	0.001 – 5.000 mL/min	0.01 – 10.00 mL/min	0.1 – 40.0 mL/min
Flow Rate Increment	0.001 mL/min	0.01 mL/min	0.1 mL/min
Flow Rate Accuracy*	±2% (0.500 – 5.000 mL/min; 80:20 Water/IPA; 1,000 psi)	±2% (1.00 – 10.00 mL/min; 80:20 Water/IPA; 1,000 psi)	±2% (4.0 - 40.0 mL/min; 80:20 Water/IPA; 1,000 psi)
Flow Reproducibility	1% RSD (0.500 – 5.000 mL/min; 80:20 Water/IPA; 1,000 psi)	1% RSD (1.00 – 10.00 mL/min; 80:20 Water/IPA; 1,000 psi)	1% RSD (0.5 – 40.0 mL/min; 80:20 Water/IPA; 1,000 psi)
Maximum Delivery Pressure	5,000 psi (PEEK) 6,000 psi (Stainless)	5,000 psi (PEEK) 6,000 psi (Stainless)	1,500 psi
Pressure Accuracy	±50 psi		
Pulsation	≤1.5% @ 1 mL/min and 80:20 Water/IPA; 1,000 psi	≤1.5% @ 1 mL/min and 80:20 Water/IPA; 1,000 psi	≤2.0% @ 4 mL/min and 80:20 Water/IPA; 1,000 psi
Piston Displacement	25.1 µL	50.3 μL	201 µL
Piston Wash	Self-flushing pump heads – continuous wash without auxiliary pump		
Wetted Materials	<b>PEEK pumps may include:</b> PEEK, Synthetic Ruby, Sapphire, Zirconia, UHMWPE, FFKM, PFA, ETFE <b>Stainless Steel pumps may include:</b> 316 Stainless Steel, PEEK, Synthetic Ruby, Sapphire, Zirconia, UHMWPE, PFA, PTFE, ETFE		
Dimensions (H x W x D)	6.4" x 7.0" x 16.0" (16.3 x 17.8 x 40.6 cm)		
Weight	15.5 lbs (7.0 kg)		
Power	100 – 240 VAC (±10%), 50 – 60 Hz, 45 W		
Front Panel	5-digit LED to monitor flow rate, pressure, and indicate parameters and alarms. Run/Stop, Prime, and menu keys, seven status indicators, Increase/Decrease displayed parameters.		
Communication	RS-232, micro-USB, LAN (serial communications) Run/Stop TTL, Analog flow control (0 –10 V, 4 –20 mA)		
Viscosity**	0.5 – 3.0 cP	0.5 – 5.0 cP	0.5 – 9.4 cP
Liquid Temperature	0 – 82 °C		
Environment	Indoor use only (Pollution degree 2)		
Altitude	Up to 2000 m (6500 ft)		
Ambient Temperature	10 – 30 °C		
Humidity	20 – 90% relative humidity		

\*Flow Rate is dependent on solvent selection and operating pressure

\*\*Range of fluid viscosities where published flow accuracy is maintained

### All SSI Pumps carry a **3-Year Warranty**

Teledyne SSI

349 North Science Park Road, State College, PA 16803 814.234.7311 | ssi\_sales@teledyne.com

teledynessi.com

*Teledyne SSI is continually improving its products and reserves the right to change product specifications, replacement parts, schematics, and instructions without notice.* 

