



- Cavity enhanced conversion for your selected wavelengths bands (1.4-1.9 micron and 2.4-4.4 micron)
- NIR /MIR dual outputs
- Choice of broadband (B) or narrowband (S)
- · Optional free-space output or fiber output


Reference Specification sheet

Optics (General)	unit	Specification Note			
Mixer Type		Intracavity OPO Mixer			
Output Wavelength - Signal	nm	Central wavelength @ 1440-1880			[1], [2]
Output Wavelength - Idler	nm	Central wavelength @ 2500-4100			[1], [2]
Optics (Output)	unit	Minimum	Typical	Maximum	Note
Output power - Signal	mW	250	300		[6]
Output power - Idler	mW	100	120		[6]
Beam quality, M ² - Signal			1.1	1.2	
Beam quality, M ² - Idler			1.2	1.5	
Linewidth	GHz		150	300	[3]
Diameter of collimated output beam	mm	0.8	1	1.2	[4]
Output beam (TEMoo) ellipicity	%		10	20	
Residual power rejection ratio at different wavelength	dB	40	45		
Output polarization state		linear @ vertical axis			
Output PER	dB	20	25		
Output beam height	mm	22.5	23	23.5	
Output beam angle	mrad	-7.5	0	7.5	
Mechanics	unit	Specification Note			
Housing dimension (L*W*H)	mm	210X90X42			
Electrics	unit	Minimum	Typical	Maximum	Note
Controller		Customized controller [5			
Environment	unit	Minimum	Typical	Maximum	Note
Storage temperature (no humidity)	°C	-20	-	70	
Operating temperature range	°C	10	25	35	
Operating relative humidity (non condensing)	%RH	0	-	85	
Vibration / Shock		Refer to ISTA-2A			
Restriction of hazardous substances directive (RoHs)		Declaration of Conformity to 2011/65/EG			

- [1] Different wavelength from 1400~1900 nm to 2400 ~ 4400 nm possible upon request
- [2] Can be tuned tens of nm in one mixer
- [3] Single longitudinal mode operation possible upon request
- [4] Fiber output for the signal port is possible upon request
- [5] Customized controller and software for operation
- [6] power level see reference bellow



- Mechanical drawing



- Reference for output power at different output wavelength

