


**SMALL, HIGH PERFORMANCE
InGaAs CAMERA**



Wildcat 640 Series

SWIR cooled camera with 640 x 512 resolution



*SMALL, HIGH PERFORMANCE
InGaAs CAMERA WITH LOW NOISE
AND HIGH DYNAMIC RANGE*

KEY FEATURES


- ◆ Frame rate up to 220 Hz or (110 Hz)
- ◆ Low noise and high dynamic range
- ◆ CameraLink or USB3 Vision interfacing options
- ◆ Small SWIR area-scan camera

The Wildcat 640 series is based on an in-house developed, temperature stabilized InGaAs detector with a 640 x 512 pixel resolution.

The cameras have standard on-board image correction featuring non-uniformity correction (NUC), bad pixel replacement (BPR) and automatic gain control (AGC). The Wildcat 640 is suitable for SWIR hyperspectral imaging, semiconductor inspection and laser beam analysis.

Wildcat 640 Series

EU based supplier



KEY PERFORMANCES

Image format/Pixel pitch	640 x 512 pixels/ 20 μ m
Detector type	InGaAs photodiode array with CTIA ROIC
Sensor temperature stabilization	TE cooler
Integration type	Snapshot - global shutter
Spectral range	900 - 1700 nm
Max frame rate (full frame)	110 Hz or 220 Hz
Power consumption	<6 W
Power supply voltage	DC 12V

FUNCTIONS & INTERFACES

Command and control	CameraLink or USB3 Vision
Connector trigger	Lemo 1B.308 (unified connector)
Camera dimensions (width x height x length)	55 mm x 55 mm x 72 mm (CL) 55 mm x 55 mm x 91.5 mm (U3V)
Optical interface	C-mount or M42
Camera weight	316 gr (CL) or 358 gr (U3V)

PRODUCT SELECTOR GUIDE

XEN-000676 (Wildcat 640 CL 100)	XEN-000662 (Wildcat 640 U3V 100)
XEN-000680 (Wildcat 640 CL 200)	XEN-000679 (Wildcat 640 U3V 200)

sales@xenics.com



xenics.com

Xenics
Photonis Group

© Xenics. XDS020. The information furnished is believed to be accurate and reliable, but is not guaranteed and is subject to change without notice. No liability is assumed by Xenics for its use. Performance data represents typical characteristics as individual product performance may vary. Customers should verify that they have the most current Xenics product information before placing orders. No claims or warranties are made as to the application of Xenics products. Texts and pictures may not be considered as contractually binding. This document may not be reproduced, in whole or in part, without the prior written consent of Xenics.