APPARATUS

CODE	PART NAME	REMARKS	
APM-00-015	apm-8	Pensky-Martens Closed Cup Flash Point Tester	

STANDARD ACCESSORIES

CODE	PART NAME	Qty	REMARKS
APM-02-001	Test Cup Assembly	1	
320-00-035	Thermofuse	1	Pack of 5, with Insulation Tube.
210-02-161	Gas Hose	1	
APM-04-431	Windscreen for apm-8	1	
	apm-8 MANUALS	1	Manuals for apm-8.

OPTIONAL ACCESSORIES

CODE	PART NAME	REMARKS	
070-00-068	Printer, BS2-80TS	Prints out test data and instrument settings.	
070-00-281	Mini USB Keyboard	Sample ID entering	

SUGGESTED SPARES for 2 YEARS

CODE	PART NAME	Qty	REMARKS
APM-02-001	Test Cup Assembly	1	Refer to Standard Accessories.
320-00-035	Thermofuse	1	Pack of 5, with Insulation Tube.
ABL-01-003	Electric Igniter, El-8	2	
APM-04-031	Temperature Sensor for apm-8	1	
APM-03-032	Flash Detector for APM-7/apm-8	1	

We reserve the right of changes without prior notice.

Printed in Japan 1201(E)

DISTRIBUTED BY

NA	AK	SCIENTIFIC
 	— 1 10	

7-10-3 Ayase, Adachi-ku, Tokyo 120-0005 JAPAN TEL: +81-3-3620-1711 FAX: +81-3-3620-1713 URL: http://www.tanaka-sci.com

E-mail: overseas-group@tanaka-sci.com

TANAKA Automatic Petroleum Tester

AUTOMATED PENSKY-MERTENS CLOSED CUP FLASH POINT TESTER

apm-8



Model apm-8 is the automated Pensky-Martens Closed Cup flash point tester from Tanaka. Based on 45 years experience of manufacturing the automated flash point testers, innovative 8th generation series has been released. The theme of 8th generation is "Ergonomic, Versatile and Premium".

- ERGONOMIC COLOR-COORDINATED DISPLAY FOR HIGH VISIBILITY FOR EVERYBODY (UNIVERSAL DESIGN) AND INTUITIVE SWITCH **OPERATION.**
- ENHANCED VERSATILITY INCLUDING USB PORT FOR OPTIONAL FLASH MEMORY OR KEYBOARD, PASSWORD PROTECTION AND DATA STRAGE.
- ALL-IN-ONE CHASSIS DESIGN: COMPACT, LIGHT-WEIGHT AND PREMIUM EXTERIOR DESIGN.
- CONFORMS TO STANDARD TEST METHOD

(ISO 2719, ASTM D93, IP34)

SINGLE ACTION SETTING

The cup cover and the stirrer are permanently mounted on a swing-arm assembly, which allows an easy handling of the test cup cover. It makes free from handling the hot cup cover after completing a test. The swing arm assembly can be lifted up to vertical position for easier test cup cleaning.

EASY OPERATION

Select a test mode and enter the expected flash point; while the instrument executes the test, you are free to do other lab work. The instrument follows the exact procedures prescribed in the test method, and the completion of the test cycle is signaled by beeps. The test result is brightly shown on the color LCD module.

INTERCHANGEABLE IGNITION SOURCE

apm-8 is equipped with both gas and electric igniter as the ignition source. It only takes a few minutes to switch from gas to electric or vice versa.

DRAFT PROTECTION SHIELD COVER

A FM4910 conforming cover insures the flame integrity. This material shall meet the numerical criterion of each index. (1)FPI(Fire Propagation Index)≤6 (2)SDI(Smoke Damage Index)≤0.4

DATA HANDLING

The unit is equipped to store up to 200 test results and export to an optional printer or to a LIMS through an RS-232 port or USB memory.

USB PORT

A USB port allows connecting USB keyboard for easy entering sample name and connecting USB flash memory for data copy to a PC or test conditions/parameters copy to the tester.



PASSWORD PROTECTION

With setting up password by the administrator, the device is protected against inadvertent change of parameters by the operator.

ALL-IN ONE DESIGN IN LIGHTWEIGHT

The all-in-one design is much lighter than old model, APM-7 by approximately 30%, which is world's smallest class in volume.

SPECIFICATIONS

All -in one, microprocess	
ISO 2719, ASTM D93, IP3	
Ambient to 370°C	
ASTM D93 A-normal, AS	
ASTM D93 B-normal, AS	
ASTM D93 C-normal, AS	
Band type heater:530W@	
Forced air cooling by fan	
5.7 inch (117 x 88mm) co	
100, 250 rpm (selectable)	
PT-100 in stainless steel	
CRC Thermocouple	
Gas ignition with automat	
Automatic correction by b	
RS-232C = 1 channel (for	
USB=1 channel (for USB	
Automatically shuts off an	
case: (a) EFP+20 °C or 370 °C i	
(b) temperature sensor is	
(d) thermofuse is blown, (
drained out, (g) test cover	
(no display) (i) Stirring mc	
LP gas or natural gas (Ma	
100/120VAC or 220/240	
720W MAX.	
170Wh for 1 test (about 6	
10°C to 35°C	
230mm (W) × 470mm (

ASTM D93 A-SPE (search), ASTM D93 A-SPE (search), ASTM D93 B-SPE (search), ASTM D93 C-SPE (search) and User custom V@115V or 500W @230V an color LCD with LED back light

l sheath

tic lighting or electric ignition. Interchangeable

built-in barometric pressure sensor

or PC or Optional Printer)

3 keyboard or USB Flash Memory)

nd the problem is reported by buzzer and display, in

is reached,

s found defective, (c) flash detector is found defective, (e) electric Igniter is blown, (f) built-in battery is found er is not set in place, (h)control computer runs away notor stopped

lax. pressure:10kPa)

VAC, 50/60Hz

60 min), 64.26gCO₂ (@ 0.378kgCO₂/1kWh)

(D) × 390mm (H) 17kg