

www.NewOpto.com

TOG/TPH 油脂分析仪



新势力光电供应**TOG/TPH油脂分析仪**,主要用于实验室或者现场在线检测:水、废水、土壤中的油脂(TOG, Total Oil and Grease)、总石油烃(TPH, Total Petroleum Hydrocarbons)。该系列**油脂分析仪**在全球范围超过 2500 套的使用量,已经成为油脂检测和监控的行业标准。

Specifications	Model CVH	Model HATR-T2	Model CH
Working Platform	Cuvette Holder	Horizontal Platform	Card Reader
Min. Detection Limit	2 nnm	8 ppm	40 ppm
(Oil in water)	-2 ppm		
Min. Detection Limit	-10 ppm	40 ppm	200 ppm
(TPH in soil)	10 ppm		
Solvent	Perchloroethylene, Freon-113, S-316	Hexane, Pentane, Vertrel MCA	Hexane, Pentane, Vertrel MCA
Component Measured	Measures all hydrocarbons	Measures hydrocarbons with a boiling point higher than the solvent - volatile hydrocarbons will be evaporated along with the solvent	Measures hydrocarbons with a boiling point higher than the solvent - volatile hydrocarbons will be evaporated along with the solvent
Instrument Repeatability	±1 ppm	±2 ppm	±4 ppm
Typical Applications	Oil in Water/Wastewater	0il in Water/Wastewater	Very high levels of Oil in Water
	Oil in Produced Water	Oil in Produced Water	TPH in Soil
	Fats, Oil & Grease (FOG in Wastewater Discharges)	Fats, Oil & Grease (FOG in Wastewater Discharges)	
	Oil in Frac Water	Oil in Frac Water	
	TPH in Soil	TPH in Soil	
	Samples with Light-End Volatile Components		

NewOpto Technology Corporation Limited

7F, Building D, Cambridge Community, No.789 Shenhua Road, Hangzhou, China 310030 Phone: +86-571-85152711 Fax: +86-571-85152722 Email: Sales@NewOpto.com



www.NewOpto.com

			W W	w.newOpto.com		
	Solvents are heavier than water		Solvents are lighter than water	Solvents are lighter than water		
Other Instructions	and require a se	eparatory funnel or	and solvent sample can be	and solvent sample can be		
	inverted vial wi	th a septa cap to	collected from the top of the	collected from the top of the		
	collect a solven	t sample.	container.	container.		
	InfraCal TOG/	TPH Analyzers				
		InfraCal IR Platfor	m Analyzer, HATR-T2 Complete w	ith HATR-T2 Stainless Steel		
	405-1009	Trough Sample St	age with Built-in Cubic Zirconia AT	'R Crystal, Power Supply and		
		Instruction Manual.				
	405-0003	InfraCal Cuvette Holder Analyzer, Model CVH Complete with CVH Sample Stage for				
		use with 10 mm Quartz Cuvette Cells, Power Supply and Instruction Manual.				
		InfraCal Card Reader Analyzer, Model CH Complete with CH Sample Stage for use wit				
	405-0002	InfraCal Reusable IR Sample Plates with Sapphire Window, Power Supply and				
		Instruction Manual.				
	Sample Handling Accessories					
	403-0012	Set of 4-10mm Quartz Cuvette Cells with Teflon stopper for use with Model CVH				
		InfraCal Reusable	IR Sample Plates with Sapphire W	indow, Set of 5 for use with Mod		
	403-0010/5	СН				
	Accessories					
	403-0018	InfraLog Serial Pr	inter Prints calibration and measu	rement data, complete with		
		sequence number, date and time. Includes all required cables.				
Ordering Information	403-0013	Carrying Case with pre-diced pluck foam. 18.5x14.6x8", 10 lbs.				
	403-0002	Cigarette Lighter Adapter Cable				
	403-0005	Dust Cover				
	Field Sampling Kits					
	403-1010	Field Sampling Kit for TPH in Soil				
	403-1011	Field Sampling Kit for TOG in Water				
	403-1063	Field Sampling Kit	Field Sampling Kit for TOG in Water			
	Replacement l	Replacement Parts				
		Universal Switchi	ng Power Supply and Line Cord for	use with InfraCal Analyzers.		
	403-0001	90-264 VAC, 50-60 Hz input, regulated 12v/25 watt output.				
	403-0014	Replacement Source/Cable Assembly				
	Additional On	Additional One and Two Year Extended Factory Warranties				
		Extended Factory	Warranty for additional One Year	(total two year factory warranty		
	EWOY	from date of shipment).				
		Extended Factory	Warranty for additional Two Year	s (total three year factory		
	EWTY	warranty from date of shipment).				
	4					

www.NewOpto.com

NewOpto Technology Corporation Limited

7F, Building D, Cambridge Community, No.789 Shenhua Road, Hangzhou, China 310030 Phone: +86-571-85152711 Fax: +86-571-85152722 Email: Sales@NewOpto.com